

HexPack™ LabPack UN/DOT approved corrugated containers are ideal for lab pack applications. With capacities that range from 3 gallons to 55 gallons (11 liters to 208 liters), the HexPack is an economical alternative to traditional fiber drums, offering significant savings for equivalent sizes. In addition, the HexPack can be completely incinerated for cost-effective hazardous and non-hazardous waste disposal.


For your added convenience, the HexPack is collapsible which allows for shipping and storing in a flat configuration for additional savings.



DOT/UN Approved HexPack LabPack Containers

SIZE	ITEM	BUNDLE QTY	PALLET QTY	INSIDE DIMENSIONS L x W x H	"A" DIA.	"B" DIA.	"C" SIDE WALL	"D" INSIDE HT.	DOT/UN SPECS
3 Gallon	UNHX034G	15	150	6.5" x 6.5" x 6.75"	11.25"	13"	6.50"	6.75"	UN4G/Y23.4/S
5 Gallon	UNHX054G	15	150	6.5" x 6.5" x 12"	11"	13.25"	6.50"	12"	UN4G/Y22.7/S
10 Gallon	UNHX104G	10	160	8" x 8" x 15.50"	13.50"	15.50"	8"	15.50"	UN4G/Y45.5/S
15 Gallon	UNHX154G	10	160	8" x 8" x 21.50"	13.75"	16"	8"	21.50"	UN4G/Y54.4/S
20 Gallon	UNHX204G	10	160	9.75" x 9.75" x 19.50"	16.75"	20"	9.75"	19.50"	UN4G/Y56.7/S
30 Gallon	UNHX304G	10	160	11" x 11" x 23.75"	18.50"	22"	11"	23.75"	UN4G/Y79.4/S
55 Gallon	UNHX554G	10	80	13.75" x 13.75" x 24"	23.75"	27.50"	13.75"	24"	UN4G/Y124.7/S

IMPORTANT NOTE: HexPack LabPack containers MUST have 3 Mil liner to meet UN certification.



HexPack LabPack Liners			
ITEM	DESCRIPTION	DIMENSIONS	CAPACITY
LHP0503	3 Mil, Clear, Polyethylene Liner	12" x 12" x 24"	Fits 3 & 5 Gallon
LHP1503	3 Mil, Clear, Polyethylene Liner	16" x 18" x 40"	Fits 10 & 15 Gallon
LHP3003	3 Mil, Clear, Polyethylene Liner	24" x 20" x 48"	Fits 20 & 30 Gallon
LHP5503	3 Mil, Clear, Polyethylene Liner	28" x 24" x 58"	Fits 55 Gallon
LHP5506	6 Mil, Clear, Polyethylene Liner	28" x 24" x 58"	Fits 55 Gallon

IMPORTANT NOTE: HexPack LabPack containers MUST have a 3 Mil liner to meet UN certification.

NOTE: UN testing of the HexPack™ LabPack corrugated drums was completed with gusseted polyethylene bags of 3 mil thickness with sufficient height to allow for closure as per the HexPack assembly and UN closing instructions. If you are packaging a *regulated* product and you decide not to utilize our high-quality Polyethylene Liner, please insure that your bag/liner specification minimally meets the above specifications for proper sealing.

If the contents being packaged are *non-regulated*, you may use any bag/liner suitable for containment of said contents and to protect the inside of the HexPack container.